

NOISE CONTROL DEMONSTRATION UNIT B600



Year 1 study

Features

- Supplied with a choice of two noise sources a motor or a fan, clearly showing real-life relevance to air-conditioning or mechanical engineers
- Allows audible experimentation on the effect of the noise frequency on the effectiveness of attenuation methods
- Clear sample tubes allow students to visually see attenuation material
- Safe for use without ear protection as noise source is enclosed
- Comprehensive Installation, Operation and Maintenance Manual Provided

Description

The B600 consists of a glass reinforced plastic instrument panel and baseboard with controllable 240v AC and 12v DC power sources. Either a 240v motor and gearbox with detachable eccentric rotor or a 12v DC fan may be fixed to resilient mounts attached to the baseboard. The mounts may be bypassed in order to demonstrate transmission of the noise through rigid mountings. Variation of the supply voltage and motor speed allows investigation of the various modes of vibration of the motor and eccentric rotor and the effects of noise source frequency.

The insertion of a large mass on the motor mounting further extends this investigation. A rigid glass reinforced plastic enclosure may be placed over either of the noise sources both with and without an absorbent acoustic lining. Openings in both ends of the box allow demonstration of the effects of small holes in the enclosure and the transmission of mechanical and aerodynamically generated noise along ducts. Removable solid linings to the acoustically lined noise attenuation tubes graphically illustrate the effectiveness of this method of attenuation. Two microphones are provided, one fixed adjacent to the noise source and the other mounted on a wand that may be moved around over the unit. Each of the two microphones may be connected to dB A filter and amplifier that illuminates a bar display on the instrument panel. The bar display indicates relative loudness by progressively illuminating a larger number of bars for a louder noise. This allows relative loudness levels to be compared visually as well as subjectively.

sales@p-a-hilton.co.uk 01794 388 382

www.p-a-hilton.co.uk



Related Laws/Applications

- · Sound and Vibration Engineering
- · Mechanical Engineering
- · Aeronautical Engineering
- Civil Engineering
- Architecture
- · Environmental Engineering
- · Building Services
- · Plant Engineering
- · Refrigeration and Air Conditioning

Learning capabilities

- Attenuation of a mechanical or aerodynamic noise source using a rigid enclosure and combining this with an absorbent acoustic lining.
- The rapid degeneration in effectiveness of the above enclosure method due to minor imperfections in construction.
- The transmission of noise along ducts and methods of attenuation using acoustic linings.
- The transmission of noise along solid paths and the methods of reduction by isolation.
- The effect of the noise frequency on the effectiveness of attenuation methods
- Rigid body modes of vibration of a resiliently mounted source and the effects of mass variation of the resonant frequencies and modes of vibration

Technical Specification

- Noise source #1: An integral 240v electric motor and gearbox.
- Noise source #2: 12v fan unit provide two noise sources.
- Variable control of both voltage sources allows speed control of both motors.
- Each of two microphones may be connected to a dBA filter and illuminated bar display to show relative loudness.
- A rigid enclosure with acoustic lining may be placed over either noise source and attachments allow investigation of sound attenuation in ducts.
- Resilient mountings and mount bypass equipment allows investigation of modes of vibration at various frequencies and transmission of noise through solids.

What's in the Box?

- 1 x B600
- 1 x Acoustic cover
- 1 x Acoustic lining
- 1 x External Microphone assembly
- 1 x Vibrating assembly
- 1 x Fan assembly
- 1 x tools
- Instruction manual
- · Packing list
- Test sheet
- · 2 year spares

Weights & Dimensions

Weight: 35 kgLength: 950mm

Width: 600mmHeight: 410mm

Essential Services

- 300W 220/240 Volts, 50Hz. (With earth/ground).
- 300W 110/120 Volts, 60Hz. (With earth/ground).

Ordering information

To order this product, please call PA Hilton quoting the following codes: B600/230 B600/115

All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure.

Copyright © 2018 P.A. Hilton Limited. All rights reserved. This technical leaflet, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of P. A.

Hilton Limited. Hi-Tech Education is a registered trade mark of P. A. Hilton Limited.