



# DISC BRAKE APPARATUS HTM38



Year 1 study

## Features

- Wall mounted apparatus.
- Can be mounted to HST1, HST100, HAC10, HAC14, HVT12f frames
- One stainless steel disc; four brake pad materials
- Three pad radii
- 360° Protractor for angle recording
- · Full set of weights and hangers provided

### Description

A brake disc is mounted vertically into a sturdy frame. A single shaft runs through the brake disc and the wall bracket supports. A cord pulley mounts to the shaft onto which is mounted a cord terminating in a Load hanger. Two bell crank levers are mounted either side of the brake disc. Through the Load hanger and calibrated weights the force is applied to the brake disc and the parameters of braking force, braking torque, normal force can be assessed. All Load hangers, and calibrated weights are supplied with the apparatus. The rotational angle of movement of the disc wheel can be viewed using the external protractor. Different brake pad materials can be tested as well as their radial position on the brake disc.

#### **Related Laws/Applications**

- Braking Force
- Braking Torque
- Friction coefficient
- Automotive
- Disc Brakes
- Levers

#### Learning capabilities

- · To determine the most effective brake pad material
- To determine the most efficient radial placing of the brake pad

#### **Technical Specification**

- Stainless steel disc wheel: Ø210mm x 3mm
- Radial positions for brake pad: 20mm intervals
- Brake pad: Ø25mm x 6mm max
- Brake pad: Brake material, aluminium, brass, nylon
- Protractor: 360°, 1° increments
- Weights set: 3 x 0.1N, 8 x 0.2N, 3 x 1N, 3 x 2N, 1 x 5N
- 2 x Load hanger

sales@p-a-hilton.co.uk 01794 388 382



#### **Essential Ancillaries**

- HAC14
- HAC10
- HST1
- HST100
- HVT12f

### What's in the Box?

- 1 x HTM38 Assembly
- 2 x Brake Pad Specimen
- 2 x Aluminium Pad Specimen
- 2 x Brass Pad Specimen
- 2 x Nylon Pad Specimen
- 1 x Hanger
- 3 x 0.1N, 8 x 0.2N, 3 x 1N, 3 x 2N, 1 x 5N weights
- · Spare Cord
- Instruction manual
- Packing list
- Test sheet

# You might also like

- HFN3
- HFN11
- HFN1

# Weights & Dimensions

- Weight: 8 kg
- Length: 450mm
- Width: 200mm
- Height: 260mm

#### **Essential Services**

· Sturdy vertical support

### **Operational Conditions**

- Storage temperature: -10°C to +70°C
- Operating temperature range: +10°C to +50°C
- Operating relative humidity range: 0 to 95%, non condensing

#### **Ordering information**

To order this product, please call PA Hilton quoting the following code: HTM38

All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure. Copyright © 2018 P.A. Hilton Limited. All rights reserved. This technical leaflet, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of P. A. Hilton Limited. Hi-Tech Education is a registered trade mark of P. A. Hilton Limited. COUNTRY OF ORIGIN - UK WARRANTY PERIOD - 5 YEARS

| 2